



EXPERIENCE THE DIFFERENCE
YOUR SECURITY & SAFETY PRODUCTS

RESPIRATORY VENTILATORS YH-830




LEARN MORE:

<http://c4icommunication.com>

Respiratory Ventilators

YH-830

- Maximum inhale pressure 30cmH₂O, with separate humidifier, better humidification
- With ST and target tidal volume mode settings
- Fast rise time
- Normal inhalation intensity, respiration rate is 54 times / min, and each exhalation triggers the ventilator perfectly. Easily keep in sync.
- Good synchronization with big flow



Description

The YH-830 Bi-level device is indicated for treatment of sleep apnea hyponea syndrome in patients weighing more than 66lb (30kg). It is intended both for home use and hospital use.

The water tank is intended for single patient use in the home environment and re-use in a hospital/institutional environment.



- Mode: CPAP, S, T, ST, VGPS
- Pressure: 4-30 cm H₂O
- Trigger adjustment
- Cycle adjustment
- Slope adjustment
- Noise less than 32 dB(A)
- With YF-01 mask, humidifier and SD card
- Water tank and power adapter



Vented mask for NIV treatment



YF-01



YF-02



Noise: <26 dBa
Vented mask
pressure range from 4-30 cmH₂O

Noise: <26 dBa
Vented mask
pressure range from 4-30 cmH₂O

